

# Track almost any sample in the lab

## B-7425 laboratory label



The B-7425 laboratory label is an excellent solution to track samples. It is designed to stay attached and remain legible in a wide range of sample collection, sample processing, microbiology and cryogenic applications.

### An all-round laboratory label

- stays attached in liquid nitrogen, freezers, hot water baths, autoclaves
- remains legible when exposed to laboratory chemicals including DMSO, Xylene, IPA, ethanol
- ideal to identify vials, tubes, slides, well plates and other specimen containers made out of glass, stainless steel or polypropylene
- can be printed in the lab with Brady's portable printers and a selection of benchtop printing systems



### Print on-site

The B-7425 laboratory label can be printed by Brady in line with your specifications. The label can also be printed on-site in any laboratory with Brady printers including BMP21-LAB, BMP51, BMP61, BMP71, BBP12, BradyPrinter M611, BradyPrinter i3300, BradyPrinter i5100, BradyPrinter i7100 and BradyJet2000. For optimal performance, it should be printed with the R6400, R4300 or R6200 ink ribbons.





## B-7425 Vial/tube labels

Brady's vial and test tube labels are designed to withstand extreme laboratory solvents like Xylene, Ethanol, Alcohol and DMSO, ensuring that the specimen identification is always legible - and will not smear, fade or fall off.





Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Label Length B (m)	Diameter C (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Compatibility	Printer Ribbon Series	Labels per Roll	Labels per Row
<b>0.6 ml</b>													
⊙	B-7425	<b>F N A H</b>	9.53	-	6.40	-	-	-	M21-375-7425	BMP21-PLUS, BMP21-LAB	R4300	1	-
<b>1.0 - 2.0 ml</b>													
▲	B-7425J	<b>F N A H</b>	20.96	6.35	-	-	-	-	J20-257-7425J	J2000	-	1500	1
<b>1.0 - 8.0 ml</b>													
⊕	B-7425J	<b>F N A H</b>	25.40	9.53	-	9.53	25.40	9.53	J20-249-7425J	J2000	-	1500	1
⬡	B-7425J	<b>F N A H</b>	25.40	9.53	-	-	-	-	J20-152-7425J	J2000	-	2000	2
▲	B-7425J	<b>F N A H</b>	38.10	44.45	-	-	-	-	J20-258-7425J	J2000	-	900	1
<b>1.0 ml</b>													
▲	B-7425J	<b>F N A H</b>	33.02	15.24	-	-	-	-	J20-256-7425J	J2000	-	1500	1
<b>1.5 - 2.0 ml</b>													
⊕	B-7425J	<b>F N A H</b>	25.40	12.70	-	11.18	-	-	J20-251-7425J	J2000	-	1500	1
<b>1.5 ml</b>													
⊙	B-7425	<b>F N A H</b>	12.70	-	6.40	-	-	-	M21-500-7425	BMP21-PLUS, BMP21-LAB	R4300	1	-
<b>2.0 - 8.0 ml</b>													
▲	B-7425J	<b>F N A H</b>	25.40	12.70	-	-	-	-	J20-59-7425J	J2000	-	2000	1
⬡	B-7425J	<b>F N A H</b>	25.40	19.05	-	-	-	-	J20-88-7425J	J2000	-	2000	2
▲	B-7425J	<b>F N A H</b>	25.40	25.40	-	-	-	-	J20-179-7425J	J2000	-	1500	1
⬡	B-7425J	<b>F N A H</b>	38.10	12.70	-	-	-	-	J20-37-7425J	J2000	-	1500	2
<b>2.0 - 50.0 ml</b>													
⊙	B-7425	<b>F N A H</b>	19.05	-	6.40	-	-	-	M21-750-7425	BMP21-PLUS, BMP21-LAB	R4300	1	-
<b>14.0 - 15.0 ml</b>													
▲	B-7425J	<b>F N A H</b>	38.10	19.05	-	-	-	-	J20-136-7425J	J2000	-	1500	1
<b>15.0 ml</b>													
∞	B-7425J	<b>F N A H</b>	28.58	-	30.48	-	-	-	J20C-1125-7425J	J2000	-	1	1
▲	B-7425J	<b>F N A H</b>	38.10	25.40	-	-	-	-	J20-235-7425J	J2000	-	1250	1
∞	B-7425J	<b>F N A H</b>	57.15	-	30.48	-	-	-	J20C-2250-7425J	J2000	-	1	1
<b>50.0 ml</b>													
▲	B-7425J	<b>F N A H</b>	50.80	6.35	-	-	-	-	J20-151-7425J	J2000	-	2000	1
▲	B-7425J	<b>F N A H</b>	50.80	25.40	-	-	-	-	J20-137-7425J	J2000	-	1500	1
▲	B-7425J	<b>F N A H</b>	76.20	25.40	-	-	76.20	25.40	J20-18-7425J	J2000	-	1000	1

Labels are shown per vial/tube size and in order of label width. The background colours in the Order Reference column represent the material colour.

**F** Freezer environment **N** Liquid nitrogen environment **A** Autoclave environment **H** Hot water bath (100°C)



## B-7425 Well plate labels

When total tracking of all sample collections is required then Brady has a solution for Well plate identification. Our well plate labels guarantee crystal clear text and barcoding for most lab environments.




Diagram	Material	Special Properties	Label Width A (mm)	Label Length B (mm)	Order Reference	Printer Compatibility	Printer Ribbon Series	Labels per Roll
⊙	B-7425	<b>F N A H</b>	9.53	6.40	M21-375-7425	BMP21-PLUS, BMP21-LAB	R4300	1
⊙	B-7425	<b>F N A H</b>	12.70	6.40	M21-500-7425	BMP21-PLUS, BMP21-LAB	R4300	1
⊙	B-7425	<b>F N A H</b>	19.05	6.40	M21-750-7425	BMP21-PLUS, BMP21-LAB	R4300	1



## B-7425J Bottles/flasks & dishes

Brady's labels for bottles, flasks and dishes are easy to handle and flexible. This enables the labels to be placed on curved containers and remain attached and legible, even after being subjected to freezing, liquid nitrogen and heat.




Diagram	Material	Special Properties	Label Width A (mm)	Label Height B (mm)	Printable Area Width PW (mm)	Printable Area Height PH (mm)	Order Reference	Printer Compatibility	Labels per Roll	Labels per Row
▲	B-7425J	<b>F N A H</b>	50.80	12.70	-	-	J20-53-7425J	J2000	2000	1
▲	B-7425J	<b>F N A H</b>	55.00	85.09	55.19	85.09	J20-260-7425J	J2000	340	1
▲	B-7425J	<b>F N A H</b>	75.00	109.98	74.96	109.98	J20-261-7425J	J2000	270	1
▲	B-7425J	<b>F N A H</b>	105.00	154.90	104.90	154.90	J20-262-7425J	J2000	200	1

The background colours in the Order Reference column represent the material colour.

**F** Freezer environment **N** Liquid nitrogen environment **A** Autoclave environment **H** Hot water bath (100°C)



## B-7425-AC Sterilisation indicating label

Sterilisation indicating labels provide users with proof of sterilisation. They are ideal for a broad range of laboratory processes including sample tracking, inventory management, general tracking, and glassware or tray identification.




Diagram	Material	Label Width A (mm)	Label Height B (mm)	Order Reference	Printer Compatibility	Printer Ribbon Series	Labels per Roll	Labels per Row
▲	B-7425	38.10	25.40	B33-235-7425-AC	i3300	B30 Monocolour	1250	1
▲	B-7425	38.10	25.40	THT-235-7425-2-AC	BBP12, BBP72, i7100, i5100	R4300	2000	1
▲	B-7425	50.80	25.40	B33-137-7425-AC	i3300	B30 Monocolour	1500	1
▲	B-7425	50.80	25.40	THT-137-7425-2-AC	BBP12, BBP72, i7100, i5100	R4300	2000	1

